



PRODUCT-DETAILS

ACH580-BDR-414A-4+B058

No Description Available

General Information	
Global Commercial Alias	ACH580-BDR-414A-4+B058
Product ID	3AUD0000000040
ABB Type Designation	ACH580-BDR-414A-4+B058
Catalog Description	No Description Available
Long Description	The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V. The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

Additional Information	
ABB Type Designation	ACH580-BDR-414A-4+B058
Country of Origin	United States (US)
Customs Tariff Number	85044080
Frequency (f)	50/60 Hz
Global Commercial Alias	ACH580-BDR-414A-4+B058
Gross Weight	0 kg
Made To Order	No
Medium Description	The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V. The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Product Name	AC Drive
Product Net Weight	0 kg
Product Type	ACH580__Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACH580-BDR-414A-4+B058