



PRODUCT-DETAILS

ACH580-3BDR-052A-4+B056

No Description Available

General Information

| | |
|-------------------------|--------------------------|
| Global Commercial Alias | ACH580-3BDR-052A-4+B056 |
| Product ID | 3AUD0000000749 |
| ABB Type Designation | ACH580-3BDR-052A-4+B056 |
| Catalog Description | No Description Available |

Additional Information

| | |
|---|----------------------------|
| ABB Type Designation | ACH580-3BDR-052A-4+B056 |
| Country of Origin | United States (US) |
| Customs Tariff Number | 85044080 |
| Degree of Protection | IP55 |
| Enclosure Type NEMA | Type12 |
| Frequency (f) | 50/60 Hz |
| Global Commercial Alias | ACH580-3BDR-052A-4+B056 |
| Gross Weight | 0 kg |
| Input Voltage (U_{in}) | 440 ... 480 V |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Number of Phases | 3 |
| Order Multiple | 1 piece |
| Output Current, Light-Overload Use (UL) | 52 A |
| Output Power, Light-Overload Use (UL) | 40 Hp |
| Product Name | AC Drive |
| Product Net Weight | 0 kg |
| Product Type | ACH580_Frequency_Converter |
| Quote Only | No |
| Selling Unit of Measure | piece |

| Short Description | ACH580-3BDR-052A-4+B056 |
|-------------------|-------------------------|
|-------------------|-------------------------|