

PRODUCT-DETAILS

ACH580-PDR-169A-2+C170

No Description Available

General Information

Global Commercial Alias	ACH580-PDR-169A-2+C170
Product ID	3AUD0000001444
ABB Type Designation	ACH580-PDR-169A-2+C170
Catalog Description	No Description Available
Long Description	<p>The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p>

Additional Information

ABB Type Designation	ACH580-PDR-169A-2+C170
Country of Origin	United States (US)
Customs Tariff Number	85044080
Global Commercial Alias	ACH580-PDR-169A-2+C170
Gross Weight	0 kg
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Product Name	AC Drive
Product Net Weight	0 kg
Product Type	ACH580__Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACH580-PDR-169A-2+C170