



## PRODUCT-DETAILS

# ACH580-3PCR-065A-4+B058

## No Description Available

### General Information

Global Commercial Alias	ACH580-3PCR-065A-4+B058
Product ID	3AUD0000001517
ABB Type Designation	ACH580-3PCR-065A-4+B058
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	ACH580-3PCR-065A-4+B058
Country of Origin	United States (US)
Customs Tariff Number	85044080
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Global Commercial Alias	ACH580-3PCR-065A-4+B058
Gross Weight	0 kg
Input Voltage (U <sub>in</sub> )	440 ... 480 V
Made To Order	No
Minimum Order Quantity	1 piece
Number of Phases	3
Order Multiple	1 piece
Output Current, Light-Overload Use (UL)	65 A
Output Power, Light-Overload Use (UL)	50 Hp
Product Name	AC Drive
Product Net Weight	0 kg
Product Type	ACH580__Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACH580-3PCR-065A-4+B058