



PRODUCT-DETAILS

ACH580-3BCR-414A-4+B056

No Description Available

General Information

Global Commercial Alias	ACH580-3BCR-414A-4+B056
Product ID	3AUD0000003182
ABB Type Designation	ACH580-3BCR-414A-4+B056
Catalog Description	No Description Available

Additional Information

ABB Type Designation	ACH580-3BCR-414A-4+B056
Country of Origin	United States (US)
Customs Tariff Number	85044080
Degree of Protection	IP55
Enclosure Type NEMA	Type12
Frequency (f)	50/60 Hz
Global Commercial Alias	ACH580-3BCR-414A-4+B056
Gross Weight	0 kg
Input Voltage (U_{in})	440 ... 480 V
Made To Order	No
Minimum Order Quantity	1 piece
Number of Phases	3
Order Multiple	1 piece
Output Current, Light-Overload Use (UL)	414 A
Output Power, Light-Overload Use (UL)	350 Hp
Product Name	AC Drive
Product Net Weight	0 kg
Product Type	ACH580_Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece

Short Description	ACH580-3BCR-414A-4+B056
-------------------	-------------------------