



PRODUCT-DETAILS

ACH580-3BDR-302A-4+B058

No Description Available

General Information

Global Commercial Alias	ACH580-3BDR-302A-4+B058
Product ID	3AUD0000003215
ABB Type Designation	ACH580-3BDR-302A-4+B058
Catalog Description	No Description Available

Additional Information

ABB Type Designation	ACH580-3BDR-302A-4+B058
Country of Origin	United States (US)
Customs Tariff Number	85044080
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Global Commercial Alias	ACH580-3BDR-302A-4+B058
Gross Weight	0 kg
Input Voltage (U_{in})	440 ... 480 V
Made To Order	No
Minimum Order Quantity	1 piece
Number of Phases	3
Order Multiple	1 piece
Output Current, Light-Overload Use (UL)	302 A
Output Power, Light-Overload Use (UL)	250 Hp
Product Name	AC Drive
Product Net Weight	0 kg
Product Type	ACH580__Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACH580-3BDR-302A-4+B058