



PRODUCT-DETAILS

ACQ580-0P-156A-4+C192+F289

ACQ580-0P-156A-4+C192+F289

General Information

Global Commercial Alias	ACQ580-0P-156A-4+C192+F289
Product ID	3AUD0000003518
ABB Type Designation	ACQ580-0P-156A-4+C192+F289
Catalog Description	ACQ580-0P-156A-4+C192+F289

Long Description

The ACS580-0P Packaged Drive includes an ACS580 drive in a UL (NEMA) Type 1 as standard, or optional 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACS580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

Additional Information

ABB Type Designation	ACQ580-0P-156A-4+C192+F289
Country of Origin	United States (US)
Customs Tariff Number	85044080
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frame Size	Undefined
Frequency (f)	50/60 Hz
Global Commercial Alias	ACQ580-0P-156A-4+C192+F289
Gross Weight	0 kg
Input Voltage (U_{in})	440 ... 480 V
Invoice Description	ACQ580-0P-156A-4+C192+F289
Made To Order	No
Medium Description	<p>The ACS580-0P Packaged Drive includes an ACS580 drive in a UL (NEMA) Type 1 as standard, or optional 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACS580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p>
Minimum Order Quantity	1 piece
Number of Phases	3
Order Multiple	1 piece

Output Current, Heavy-Duty Use (UL)	124 A
Output Current, Light-Overload Use (UL)	156 A
Output Power, Heavy-Duty Use (UL)	100 Hp
Output Power, Light-Overload Use (UL)	125 Hp
Product Name	AC Drive
Product Net Depth / Length	23 in
Product Net Height	52.3 in
Product Net Weight	431 lb
Product Net Width	32.5 in
Product Type	Undefined
Quote Only	No
Rated Input Voltage (UL)	460 V
Selling Unit of Measure	piece
UNSPSC	39121007