

PRODUCT-DETAILS

ACH580-BCR-414A-4+B056

HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 350 Hp, 414 A (ACH580-BCR-414A-4+B056)



General Information

| | |
|-------------------------|--|
| Global Commercial Alias | ACH580-BCR-414A-4+B056 |
| Product ID | 3AUD0000003728 |
| ABB Type Designation | ACH580-BCR-414A-4+B056 |
| Catalog Description | HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US, UL: Pld 350 Hp, 414 A (ACH580-BCR-414A-4+B056) |
| Long Description | <p>The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p> |

Ordering

| | |
|-------------------------|--------------------|
| Country of Origin | United States (US) |
| Customs Tariff Number | 85044080 |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Order Multiple | 1 piece |
| Quote Only | No |
| Selling Unit of Measure | piece |

| Dimensions | |
|--------------------|------|
| Product Net Weight | 0 kg |

| Technical | |
|----------------------------------|---------------|
| Number of Phases | 3 |
| Degree of Protection | IP55 |
| Enclosure Type NEMA | Type12 |
| Frequency (f) | 50/60 Hz |
| Input Voltage (U _{in}) | 440 ... 480 V |

| Additional Information | |
|------------------------|----------|
| Product Name | AC Drive |

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BCR - HVAC packaged drive with e-clipse bypass and circuit breaker disconnect US



