

PRODUCT-DETAILS

# ACH580-BDR-052A-6+B058

HVAC packaged drive with e-clipse bypass and disconnect US, UL: Pld 50 Hp, 52 A (ACH580-BDR-052A-6+B058)



## General Information

Global Commercial Alias	ACH580-BDR-052A-6+B058
Product ID	3AUD0000004276
ABB Type Designation	ACH580-BDR-052A-6+B058
Catalog Description	HVAC packaged drive with e-clipse bypass and disconnect US, UL: Pld 50 Hp, 52 A (ACH580-BDR-052A-6+B058)
Long Description	<p>The ACH580 with ABB E-Clipse bypass has an integrated UL (NEMA) Type 1, 12 or 3R enclosure with a bypass motor starter and is available from 1 to 350 hp at 230/460/575 V.</p> <p>The ACH580 with ABB E-Clipse bypass provides an input disconnect switch or circuit breaker with door mounted and interlocked switch (padlockable in the OFF position), a bypass starter, electronic motor overload protection, a door mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability</p>

## Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	0 kg

Technical	
Number of Phases	3
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Input Voltage (U <sub>in</sub> )	500 ... 600 V

Additional Information	
Product Name	AC Drive

Categories
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-BDR - HVAC packaged drive with e-clipse bypass and disconnect US

