

PRODUCT-DETAILS

# ACH580-PDR-144A-6+B058

HVAC drive with disconnect US, UL: Pld 150 Hp, 144 A (ACH580-PDR-144A-6+B058)



## General Information

Global Commercial Alias	ACH580-PDR-144A-6+B058
Product ID	3AUD0000004295
ABB Type Designation	ACH580-PDR-144A-6+B058
Catalog Description	HVAC drive with disconnect US, UL: Pld 150 Hp, 144 A (ACH580-PDR-144A-6+B058)
Long Description	The ACH580 Packaged Drive includes an ACH580 drive in a UL (NEMA) Type 1, 12 or 3R enclosure with either an input disconnect switch and fast acting fuses or an input circuit breaker. It is available from 1 to 350 hp at 230/460/575 V. The ACH580 Packaged Drive provides a door-mounted input disconnect switch (padlockable in the OFF position), electronic motor overload protection, a door-mounted control panel with graphical display for local control, provisions for external control connections, and serial communications capability

## Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece

Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Number of Phases	3
Enclosure Type NEMA	Type3R
Frequency (f)	50/60 Hz
Input Voltage (U <sub>in</sub> )	500 ... 600 V

Additional Information

Product Name	AC Drive
--------------	----------

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH580-PDR - HVAC drive with disconnect US



