



## PRODUCT-DETAILS

# ACH580-3BDR-065A-4+G390

## No Description Available

### General Information

Global Commercial Alias	ACH580-3BDR-065A-4+G390
Product ID	3AUD0000004601
ABB Type Designation	ACH580-3BDR-065A-4+G390
Catalog Description	No Description Available

### Additional Information

ABB Type Designation	ACH580-3BDR-065A-4+G390
Country of Origin	United States (US)
Customs Tariff Number	85044080
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Global Commercial Alias	ACH580-3BDR-065A-4+G390
Gross Weight	0 kg
Made To Order	No
Minimum Order Quantity	1 piece
Number of Phases	3
Order Multiple	1 piece
Output Current, Light-Overload Use (UL)	65 A
Output Power, Light-Overload Use (UL)	50 Hp
Product Name	AC Drive
Product Net Weight	0 kg
Product Type	ACH580 _Frequency Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACH580-3BDR-065A-4+G390