



PRODUCT-DETAILS

ACS880-37-0585A-3

ACS880-37-0585A-3; ACS880-37-0585A-3 PN:315kW, IN:585A

General Information

Global Commercial Alias	ACS880-37-0585A-3
Product ID	3AXD50000042665
ABB Type Designation	ACS880-37-0585A-3
Catalog Description	ACS880-37-0585A-3; ACS880-37-0585A-3 PN:315kW, IN:585A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-37-0585A-3 PN:315kW, IN:585A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical

Frame Size	R11
Ecodesign Exemption	Energy efficiency data is not provided for the drive. The low-harmonic drives are exempt from the EU ecodesign requirements (Regulation EU/2019/1781, §2.3.d).

Additional Information

Product Main Type	ACS880-37-0585A-3
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	9ECED1FE-316A-4BF4-991E-2606BB5FE13A Finland (FI)
------	---

WEEE Category4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-37 - Cabinet-built low harmonic single drive
Drives → Services → Spares and Consumables → Parts