

## PRODUCT-DETAILS

# 3AXD50000047610

# ACS560-01-02A6-4



### General Information

Product ID	3AXD50000047610
ABB Type Designation	ACS560-01-02A6-4
Catalog Description	ACS560-01-02A6-4

### Ordering

Country of Origin	India (IN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS560-01-02A6-4
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Technical

Frame Size	R1
Apparent Power Output	2.0 kV-A

Efficiency Level	IE2
Standby Loss	15 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	27 W	1.5 %	78.2 %
0 / 50 %	29 W	1.6 %	86.3 %
0 / 100 %	35 W	1.9 %	90.8 %
50 / 25 %	28 W	1.5 %	87.8 %
50 / 50 %	31 W	1.7 %	92.5 %
50 / 100 %	38 W	2.1 %	94.9 %
90 / 50 %	33 W	1.8 %	95.5 %
90 / 100 %	44 W	2.5 %	96.7 %

Temperature Rating	Maximum 50 °C
--------------------	---------------

Additional Information	
Product Main Type	ACS560-01-02A6-4
Product Name	FREQUENCY CONVERTER

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS560-01 - Wall-mounted drive	

