

PRODUCT-DETAILS

3AXD50000047641

ACS560-01-03A3-4



General Information

Product ID	3AXD50000047641
ABB Type Designation	ACS560-01-03A3-4
Catalog Description	ACS560-01-03A3-4

Ordering

Country of Origin	India (IN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS560-01-03A3-4
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical

Frame Size	R1
Apparent Power Output	2.0 kV-A

Efficiency Level	IE2
Standby Loss	15 W
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	30 W	1.3 %	80.2 %
0 / 50 %	34 W	1.5 %	87.5 %
0 / 100 %	42 W	1.8 %	91.2 %
50 / 25 %	31 W	1.4 %	89.0 %
50 / 50 %	35 W	1.5 %	93.3 %
50 / 100 %	46 W	2.0 %	95.1 %
90 / 50 %	39 W	1.7 %	95.8 %
90 / 100 %	55 W	2.4 %	96.8 %

Temperature Rating	Maximum 50 °C
--------------------	---------------

Additional Information	
Product Main Type	ACS560-01-03A3-4
Product Name	FREQUENCY CONVERTER

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS560-01 - Wall-mounted drive	

