

## PRODUCT-DETAILS

3AXD50000047643

ACS560-01-05A6-4



### General Information

Product ID	3AXD50000047643
ABB Type Designation	ACS560-01-05A6-4
Catalog Description	ACS560-01-05A6-4

### Ordering

Country of Origin	India (IN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS560-01-05A6-4
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Technical

Frame Size	R1
Apparent Power Output	4.0 kV·A
Efficiency Level	IE2
Standby Loss	15 W

Complete Drive Module  
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	45 W	1.2 %	82.1 %
0 / 50 %	52 W	1.3 %	88.3 %
0 / 100 %	71 W	1.8 %	91.2 %
50 / 25 %	47 W	1.2 %	90.1 %
50 / 50 %	55 W	1.4 %	93.7 %
50 / 100 %	79 W	2.0 %	95.1 %
90 / 50 %	61 W	1.6 %	96.1 %
90 / 100 %	91 W	2.3 %	96.8 %

Temperature RatingMaximum 50 °C

Additional Information

Product Main TypeACS560-01-05A6-4  
Product NameFREQUENCY CONVERTER

Classifications

UNSPSC39122001

Environmental

WEEE Category5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS560-01 - Wall-mounted drive

