

PRODUCT-DETAILS

3AXD50000047648

ACS560-01-025A-4



General Information

Product ID	3AXD50000047648
ABB Type Designation	ACS560-01-025A-4
Catalog Description	ACS560-01-025A-4

Ordering

Country of Origin	India (IN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS560-01-025A-4
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical

Frame Size	R3
Apparent Power Output	17 kV·A
Efficiency Level	IE2
Standby Loss	26 W

Complete Drive Module
Efficiency (61800-9-2)

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	130 W	0.8 %	87.6 %
0 / 50 %	166 W	1.0 %	91.4 %
0 / 100 %	290 W	1.7 %	92.4 %
50 / 25 %	138 W	0.8 %	93.3 %
50 / 50 %	182 W	1.1 %	95.3 %
50 / 100 %	331 W	1.9 %	95.7 %
90 / 50 %	207 W	1.2 %	97.0 %
90 / 100 %	390 W	2.3 %	97.1 %

Temperature RatingMaximum 50 °C

Additional Information

Product Main TypeACS560-01-025A-4
Product NameFREQUENCY CONVERTER

Classifications

UNSPSC39122001

Environmental

WEEE Category5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS560-01 - Wall-mounted drive

