

## PRODUCT-DETAILS

# 3AXD50000048376

# ACS560-01-246A-4



### General Information

Product ID	3AXD50000048376
ABB Type Designation	ACS560-01-246A-4
Catalog Description	ACS560-01-246A-4

### Ordering

Country of Origin	India (IN) Finland (FI)
Customs Tariff Number	85044084
Invoice Description	ACS560-01-246A-4
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Container Information

Gross Volume	79.82 dm <sup>3</sup>
--------------	-----------------------

Technical

Frame Size	R8
Apparent Power Output	170 kV-A
Efficiency Level	IE2
Standby Loss	47 W
Complete Drive Module	
Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	814 W	0.5 %	91.9 %
0 / 50 %	1125 W	0.7 %	94.1 %
0 / 100 %	2027 W	1.2 %	94.6 %
50 / 25 %	892 W	0.5 %	95.6 %
50 / 50 %	1279 W	0.8 %	96.7 %
50 / 100 %	2379 W	1.4 %	96.9 %
90 / 50 %	1513 W	0.9 %	97.8 %
90 / 100 %	3126 W	1.8 %	97.7 %

Temperature Rating	Maximum 40 °C
--------------------	---------------

Additional Information

Product Main Type	ACS560-01-246A-4
Product Name	FREQUENCY CONVERTER

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS560-01 - Wall-mounted drive

