



PRODUCT-DETAILS

ACS580-01-017A-2

ACS580-01-017A-2 PN: 4.0 kW, IN: 16.9 A

General Information

Global Commercial Alias	ACS580-01-017A-2
Product ID	3AXD50000215270
ABB Type Designation	ACS580-01-017A-2
Catalog Description	ACS580-01-017A-2 PN: 4.0 kW, IN: 16.9 A

Additional Information

ABB EcoSolutions	Yes
ABB Type Designation	ACS580-01-017A-2
Altitude	1000 m
Circular Design Principles Lifetime	3AXD10001912952
Circular Design Principles Recyclability Rate	90 %
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
End of Life Instructions	3AXD50000153893
Environmental Product Declaration - EPD	3AXD10001912952
Frame Size	R1
Global Commercial Alias	ACS580-01-017A-2
Gross Volume	10.397 dm³
Gross Weight	6.84 kg
Improved Resource Efficiency for Customers	Product Efficiency - Product considered more energy-efficient compared to similar product on market or older products from the same line Process Efficiency - Product contribute to making customer's operations more resilient and reliable Digital Efficiency - Product is digitally-supported to optimize usage and eventually optimize customer asset
Invoice Description	ACS580-01-017A-2 PN: 4.0 kW, IN: 16.9 A
Made To Order	Yes
Medium Description	ACS580-01-017A-2 PN: 4.0 kW, IN: 16.9 A
Minimum Order Quantity	1 piece
Module Function	LV AC general purpose wall-mounted drive

Offered with Extended Lifetime	Lifetime extension of customer's assets is made possible thanks to offering and the supporting services	
Order Multiple	1 piece	
Package Level 1 Depth / Length	225 mm	
Package Level 1 Gross Weight	1.74 kg	
Package Level 1 Height	370 mm	
Package Level 1 Width	526 mm	
Package Level 2 Depth / Length	0 in	
Package Level 2 Gross Weight	0 lb	
Package Level 2 Height	0 in	
Package Level 2 Width	0 in	
Product Main Type	ACS580-01	
Product Name	Frequency converter	
Product Net Depth / Length	223 mm	
Product Net Height	373 mm	
Product Net Weight	4.6 kg	
Product Net Width	125 mm	
Product Type	ACS580-01	
Quote Only	No	
Selling Unit of Measure	piece	
Short Description	ACS580-01-017A-2 PN: 4.0 kW, IN: 16.9 A	
Sound dB (A)	59 dB(A)	
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia	
Sustainable Material Content	Recycled Metal - 34 %	
Sustainable Material Content in Packaging	90 %	
WEEE B2C / B2B	Business To Business	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)	