



PRODUCT-DETAILS

ACS580-01-059A-2

ACS580-01-059A-2 PN: 15.0 kW, IN: 60 A

General Information

Global Commercial Alias	ACS580-01-059A-2
Product ID	3AXD50000215317
ABB Type Designation	ACS580-01-059A-2
Catalog Description	ACS580-01-059A-2 PN: 15.0 kW, IN: 60 A

Additional Information

ABB EcoSolutions	Yes
ABB Type Designation	ACS580-01-059A-2
Altitude	1000 m
Circular Design Principles Lifetime	3AXD10001912952
Circular Design Principles Recyclability Rate	90 %
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
End of Life Instructions	3AXD50000153893
Environmental Product Declaration - EPD	3AXD10001912952
Frame Size	R3
Global Commercial Alias	ACS580-01-059A-2
Gross Volume	22.779 dm³
Gross Weight	14.54 kg
Improved Resource Efficiency for Customers	Product Efficiency - Product considered more energy-efficient compared to similar product on market or older products from the same line Process Efficiency - Product contribute to making customer's operations more resilient and reliable Digital Efficiency - Product is digitally-supported to optimize usage and eventually optimize customer asset
Invoice Description	ACS580-01-059A-2 PN: 15.0 kW, IN: 60 A
Made To Order	Yes
Medium Description	ACS580-01-059A-2 PN: 15.0 kW, IN: 60 A
Minimum Order Quantity	1 piece
Module Function	LV AC general purpose wall-mounted drive

Offered with Extended Lifetime	Lifetime extension of customer's assets is made possible thanks to offering and the supporting services	
Order Multiple		1 piece
Package Level 1 Depth / Length		295 mm
Package Level 1 Gross Weight		2.24 kg
Package Level 1 Height		390 mm
Package Level 1 Width		600 mm
Package Level 2 Depth / Length		0 in
Package Level 2 Gross Weight		0 lb
Package Level 2 Height		0 in
Package Level 2 Width		0 in
Product Main Type		ACS580-01
Product Name		Frequency converter
Product Net Depth / Length		229 mm
Product Net Height		490 mm
Product Net Weight		11.8 kg
Product Net Width		203 mm
Product Type		ACS580-01
Quote Only		No
Selling Unit of Measure		piece
Short Description	ACS580-01-059A-2 PN: 15.0 kW, IN: 60 A	
Sound dB (A)		76 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia	
Sustainable Material Content		Recycled Metal - 34 %
Sustainable Material Content in Packaging		90 %
WEEE B2C / B2B		Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)	