



PRODUCT-DETAILS

ACQ580-01-211A-2

ACQ580-01-211A-2 PN: 55 kW, IN: 213 A

General Information	
Global Commercial Alias	ACQ580-01-211A-2
Product ID	3AXD50000216017
ABB Type Designation	ACQ580-01-211A-2
Catalog Description	ACQ580-01-211A-2 PN: 55 kW, IN: 213 A

Additional Information	
ABB Type Designation	ACQ580-01-211A-2
Altitude	1000 m
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Frame Size	R7
Global Commercial Alias	ACQ580-01-211A-2
Gross Volume	92.47 dm ³
Gross Weight	65 kg
Invoice Description	ACQ580-01-211A-2 PN: 55 kW, IN: 213 A
Made To Order	Yes
Medium Description	ACQ580-01-211A-2 PN: 55 kW, IN: 213 A
Minimum Order Quantity	1 piece
Module Function	LV AC wall-mounted drive for water and wastewater
Order Multiple	1 piece
Package Level 1 Depth / Length	992 mm
Package Level 1 Gross Weight	11 kg
Package Level 1 Height	568 mm
Package Level 1 Width	400 mm
Package Level 2 Depth / Length	39.055 in
Package Level 2 Gross Weight	24.251 lb
Package Level 2 Height	22.362 in
Package Level 2 Width	15.748 in
Product Main Type	ACQ580-01
Product Name	Frequency converter

Product Net Depth / Length	370 mm
Product Net Height	880 mm
Product Net Weight	54 kg
Product Net Width	284 mm
Product Type	ACQ580-01
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACQ580-01-211A-2 PN: 55 kW, IN: 213 A
Sound dB (A)	67 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)