



PRODUCT-DETAILS

ACQ580-01-03A9-6

ACQ580-01-03A9-6 PN: 2.2 kW, IN: 3.9 A

General Information

Global Commercial Alias	ACQ580-01-03A9-6
Product ID	3AXD50000216574
ABB Type Designation	ACQ580-01-03A9-6
Catalog Description	ACQ580-01-03A9-6 PN: 2.2 kW, IN: 3.9 A

Additional Information

ABB Type Designation	ACQ580-01-03A9-6
Altitude	1000 m
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Frame Size	R2
Global Commercial Alias	ACQ580-01-03A9-6
Gross Volume	13.51 dm³
Gross Weight	8.95 kg
Invoice Description	ACQ580-01-03A9-6 PN: 2.2 kW, IN: 3.9 A
Made To Order	Yes
Medium Description	ACQ580-01-03A9-6 PN: 2.2 kW, IN: 3.9 A
Minimum Order Quantity	1 piece
Module Function	LV AC wall-mounted drive for water and wastewater
Order Multiple	1 piece
Package Level 1 Depth / Length	225 mm
Package Level 1 Gross Weight	1.85 kg
Package Level 1 Height	370 mm
Package Level 1 Width	621 mm
Package Level 2 Depth / Length	8.858 in
Package Level 2 Gross Weight	4.079 lb
Package Level 2 Height	14.567 in
Package Level 2 Width	24.449 in
Product Main Type	ACQ580-01
Product Name	Frequency converter
Product Net Depth / Length	228.5 mm
Product Net Height	473 mm

Product Net Weight	6.6 kg
Product Net Width	125 mm
Product Type	ACQ580-01
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACQ580-01-03A9-6 PN: 2.2 kW, IN: 3.9 A
Sound dB (A)	64 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)