



PRODUCT-DETAILS

# ACQ580-01-017A-6

## ACQ580-01-017A-6 PN: 11.0 kW, IN: 17.0 A

General Information	
Global Commercial Alias	ACQ580-01-017A-6
Product ID	3AXD50000216611
ABB Type Designation	ACQ580-01-017A-6
Catalog Description	ACQ580-01-017A-6 PN: 11.0 kW, IN: 17.0 A

Additional Information	
ABB Type Designation	ACQ580-01-017A-6
Altitude	1000 m
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Frame Size	R2
Global Commercial Alias	ACQ580-01-017A-6
Gross Volume	13.51 dm <sup>3</sup>
Gross Weight	8.95 kg
Invoice Description	ACQ580-01-017A-6 PN: 11.0 kW, IN: 17.0 A
Made To Order	Yes
Medium Description	ACQ580-01-017A-6 PN: 11.0 kW, IN: 17.0 A
Minimum Order Quantity	1 piece
Module Function	LV AC wall-mounted drive for water and wastewater
Order Multiple	1 piece
Package Level 1 Depth / Length	225 mm
Package Level 1 Gross Weight	1.85 kg
Package Level 1 Height	370 mm
Package Level 1 Width	621 mm
Package Level 2 Depth / Length	8.858 in
Package Level 2 Gross Weight	4.079 lb
Package Level 2 Height	14.567 in
Package Level 2 Width	24.449 in
Product Main Type	ACQ580-01
Product Name	Frequency converter

Product Net Depth / Length	228.5 mm
Product Net Height	473 mm
Product Net Weight	6.6 kg
Product Net Width	125 mm
Product Type	ACQ580-01
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACQ580-01-017A-6 PN: 11.0 kW, IN: 17.0 A
Sound dB (A)	64 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)