



## PRODUCT-DETAILS

# ACQ580-01-032A-6

## ACQ580-01-032A-6 PN: 22 kW, IN: 32 A

### General Information

Global Commercial Alias	ACQ580-01-032A-6
Product ID	3AXD50000216642
ABB Type Designation	ACQ580-01-032A-6
Catalog Description	ACQ580-01-032A-6 PN: 22 kW, IN: 32 A

### Additional Information

ABB Type Designation	ACQ580-01-032A-6
Altitude	1000 m
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Frame Size	R3
Global Commercial Alias	ACQ580-01-032A-6
Gross Volume	22.779 dm³
Gross Weight	14.54 kg
Invoice Description	ACQ580-01-032A-6 PN: 22 kW, IN: 32 A
Made To Order	Yes
Medium Description	ACQ580-01-032A-6 PN: 22 kW, IN: 32 A
Minimum Order Quantity	1 piece
Module Function	LV AC wall-mounted drive for water and wastewater
Order Multiple	1 piece
Package Level 1 Depth / Length	295 mm
Package Level 1 Gross Weight	2.24 kg
Package Level 1 Height	390 mm
Package Level 1 Width	600 mm
Package Level 2 Depth / Length	11.614 in
Package Level 2 Gross Weight	4.938 lb
Package Level 2 Height	15.354 in
Package Level 2 Width	23.622 in
Product Main Type	ACQ580-01
Product Name	Frequency converter
Product Net Depth / Length	229 mm
Product Net Height	490 mm

Product Net Weight	11.8 kg
Product Net Width	203 mm
Product Type	ACQ580-01
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACQ580-01-032A-6 PN: 22 kW, IN: 32 A
Sound dB (A)	76 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)