



PRODUCT-DETAILS

ACQ580-01-052A-6

ACQ580-01-052A-6 PN: 37 kW, IN: 52 A

General Information

Global Commercial Alias	ACQ580-01-052A-6
Product ID	3AXD50000216666
ABB Type Designation	ACQ580-01-052A-6
Catalog Description	ACQ580-01-052A-6 PN: 37 kW, IN: 52 A

Additional Information

ABB Type Designation	ACQ580-01-052A-6
Altitude	1000 m
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Frame Size	R5
Global Commercial Alias	ACQ580-01-052A-6
Gross Volume	43.836 dm³
Gross Weight	35.68 kg
Invoice Description	ACQ580-01-052A-6 PN: 37 kW, IN: 52 A
Made To Order	Yes
Medium Description	ACQ580-01-052A-6 PN: 37 kW, IN: 52 A
Minimum Order Quantity	1 piece
Module Function	LV AC wall-mounted drive for water and wastewater
Order Multiple	1 piece
Package Level 1 Depth / Length	835 mm
Package Level 1 Gross Weight	6.88 kg
Package Level 1 Height	521 mm
Package Level 1 Width	295 mm
Package Level 2 Depth / Length	32.874 in
Package Level 2 Gross Weight	15.168 lb
Package Level 2 Height	20.512 in
Package Level 2 Width	11.614 in
Product Main Type	ACQ580-01
Product Name	Frequency converter
Product Net Depth / Length	295 mm
Product Net Height	732 mm

Product Net Weight	28.3 kg
Product Net Width	203 mm
Product Type	ACQ580-01
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACQ580-01-052A-6 PN: 37 kW, IN: 52 A
Sound dB (A)	63 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)