



PRODUCT-DETAILS

# ACQ580-01-242A-6

ACQ580-01-242A-6 PN: 180 kW, IN: 242 A

## General Information

Global Commercial Alias	ACQ580-01-242A-6
Product ID	3AXD50000216734
ABB Type Designation	ACQ580-01-242A-6
Catalog Description	ACQ580-01-242A-6 PN: 180 kW, IN: 242 A

## Additional Information

ABB Type Designation	ACQ580-01-242A-6
Altitude	1000 m
CN8	85044084
Country of Origin	Finland (FI)
Customs Tariff Number	85044084
Frame Size	R9
Global Commercial Alias	ACQ580-01-242A-6
Gross Volume	151.692 dm <sup>3</sup>
Gross Weight	111 kg
Invoice Description	ACQ580-01-242A-6 PN: 180 kW, IN: 242 A
Made To Order	Yes
Medium Description	ACQ580-01-242A-6 PN: 180 kW, IN: 242 A
Minimum Order Quantity	1 piece
Module Function	LV AC wall-mounted drive for water and wastewater
Order Multiple	1 piece
Package Level 1 Depth / Length	1145 mm
Package Level 1 Gross Weight	14 kg
Package Level 1 Height	630 mm
Package Level 1 Width	485 mm
Package Level 2 Depth / Length	45.079 in
Package Level 2 Gross Weight	30.865 lb
Package Level 2 Height	24.803 in
Package Level 2 Width	19.094 in
Product Main Type	ACQ580-01
Product Name	Frequency converter

Product Net Depth / Length	418 mm
Product Net Height	955 mm
Product Net Weight	97 kg
Product Net Width	380 mm
Product Type	ACQ580-01
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACQ580-01-242A-6 PN: 180 kW, IN: 242 A
Sound dB (A)	68 dB(A)
Stocked At (Warehouses)	Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)