

PRODUCT-DETAILS

ACS880-04FXT-1576A-7

ACS880-04FXT-1576A-7 PN:1400kW, IN:1576A



General Information

Global Commercial Alias	ACS880-04FXT-1576A-7
Product ID	3AXD50000312443
ABB Type Designation	ACS880-04FXT-1576A-7
Catalog Description	ACS880-04FXT-1576A-7 PN:1400kW, IN:1576A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044086
Invoice Description	ACS880-04FXT-1576A-7 PN:1400kW, IN:1576A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	224 kg
Product Net Depth /	477 mm

Length	
Product Net Height	1733 mm
Product Net Width	620 mm

Technical

Frame Size	4xR11F
Ecodesign Exemption	Energy efficiency data is not provided for the drive module/module package. The drive modules/module packages are not considered as VSD and are not in the scope of the EU ecodesign requirements (Regulation EU/2019/1781).

Additional Information

Product Main Type	ACS880-04FXT-1576A-7
Product Name	Frequency Converter

Classifications

UNSPSC	39122001
--------	----------

Environmental

SCIP	b717701d-41f1-4695-811b-cee3682beed6 Finland (FI)
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04FXT - Single drive module package (flange-mounted)

