

PRODUCT-DETAILS

3AXD50000447831

, IEC: Pn 710 kW, 1250 A (ACS880-04-1250A-3)



General Information

Product ID	3AXD50000447831
ABB Type Designation	ACS880-04-1250A-3
Catalog Description	, IEC: Pn 710 kW, 1250 A (ACS880-04-1250A-3)

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-04-1250A-3
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical

Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type

Frequency (f)	50/60 Hz
Input Voltage (U_{in})	380 ... 415 V
Mounting Type	Module for cabinet building
Output Current, Heavy-Duty Use (I_{HD})	935 A
Output Current, Light-Overload Use (I_{LD})	1200 A
Output Current, Normal Use (I_n)	1250 A
Output Power, Heavy-Duty Use (P_{HD})	500 kW
Output Power, Light-Overload Use (P_{LD})	630 kW
Output Power, Normal Use (P_n)	710 kW

Additional Information

Product Name	Frequency converter
--------------	---------------------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04 - Single drive module



