

PRODUCT-DETAILS

3AXD50000448333

, IEC: Pn 900 kW, 1320 A (ACS880-04-1320A-5)



General Information

Product ID	3AXD50000448333
ABB Type Designation	ACS880-04-1320A-5
Catalog Description	, IEC: Pn 900 kW, 1320 A (ACS880-04-1320A-5)

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-04-1320A-5
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical

Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type

Frequency (f)	50/60 Hz
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Module for cabinet building
Output Current, Heavy-Duty Use (I_{HD})	987 A
Output Current, Light-Overload Use (I_{LD})	1267 A
Output Current, Normal Use (I_n)	1320 A
Output Power, Heavy-Duty Use (P_{HD})	710 kW
Output Power, Light-Overload Use (P_{LD})	900 kW
Output Power, Normal Use (P_n)	900 kW

Additional Information

Product Name	Frequency converter
--------------	---------------------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04 - Single drive module



