

PRODUCT-DETAILS

**3AXD50000448524**

, IEC: Pn 1400 kW, 1450 A (ACS880-04-1450A-7)



## General Information

Product ID	3AXD50000448524
ABB Type Designation	ACS880-04-1450A-7
Catalog Description	, IEC: Pn 1400 kW, 1450 A (ACS880-04-1450A-7)

## Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-04-1450A-7
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Technical

Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type

Frequency (f)	50/60 Hz
Input Voltage ( $U_{in}$ )	525 ... 690 V
Mounting Type	Module for cabinet building
Output Current, Heavy-Duty Use ( $I_{HD}$ )	1085 A
Output Current, Light-Overload Use ( $I_{LD}$ )	1392 A
Output Current, Normal Use ( $I_n$ )	1450 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	1000 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	1250 kW
Output Power, Normal Use ( $P_n$ )	1400 kW

Additional Information

Product Name	Frequency converter
--------------	---------------------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04 - Single drive module



