

PRODUCT-DETAILS

3AXD50000448609
, IEC: Pn 1400 kW, 2610 A (ACS880-04-2610A-3+A004)



General Information	
Product ID	3AXD50000448609
ABB Type Designation	ACS880-04-2610A-3+A004
Catalog Description	, IEC: Pn 1400 kW, 2610 A (ACS880-04-2610A-3+A004)

Ordering	
Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-04-2610A-3+A004
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical	
Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type

Frequency (f)	50/60 Hz
Input Voltage (U _{in})	380 ... 415 V
Mounting Type	Module for cabinet building
Output Current, Heavy-Duty Use (I _{HD})	1952 A
Output Current, Light-Overload Use (I _{LD})	2506 A
Output Current, Normal Use (I _n)	2610 A
Output Power, Heavy-Duty Use (P _{HD})	1000 kW
Output Power, Light-Overload Use (P _{LD})	1400 kW
Output Power, Normal Use (P _n)	1400 kW

Additional Information

Product Name	Frequency converter
--------------	---------------------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04 - Single drive module



