

PRODUCT-DETAILS

**3AXD50000448647**  
**, IEC: Pn 1100 kW, 1580 A (ACS880-04-1580A-5+A004)**



General Information	
Product ID	3AXD50000448647
ABB Type Designation	ACS880-04-1580A-5+A004
Catalog Description	, IEC: Pn 1100 kW, 1580 A (ACS880-04-1580A-5+A004)

Ordering	
Country of Origin	Finland (FI)
Customs Tariff Number	85044088
Invoice Description	ACS880-04-1580A-5+A004
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Technical	
Number of Phases	3
Degree of Protection	IP00
Enclosure Type NEMA	Open Type

Frequency (f)	50/60 Hz
Input Voltage (U <sub>in</sub> )	380 ... 500 V
Mounting Type	Module for cabinet building
Output Current, Heavy-Duty Use (I <sub>HD</sub> )	1182 A
Output Current, Light-Overload Use (I <sub>LD</sub> )	1517 A
Output Current, Normal Use (I <sub>n</sub> )	1580 A
Output Power, Heavy-Duty Use (P <sub>HD</sub> )	800 kW
Output Power, Light-Overload Use (P <sub>LD</sub> )	1000 kW
Output Power, Normal Use (P <sub>n</sub> )	1100 kW

Additional Information

Product Name	Frequency converter
--------------	---------------------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04 - Single drive module



