



PRODUCT-DETAILS

ACQ580-PC-011A-6

LV AC Packaged drive with circuit breaker and fuse, UL: Pld 10 Hp, 11 A, 575 V (ACQ580-PC-011A-6)

General Information

Global Commercial Alias	ACQ580-PC-011A-6
Product ID	3AXD50000465330
ABB Type Designation	ACQ580-PC-011A-6
EAN	6438177601708
Catalog Description	LV AC Packaged drive with circuit breaker and fuse, UL: Pld 10 Hp, 11 A, 575 V (ACQ580-PC-011A-6)

Long Description

The ACQ580-PC drives deliver the ACQ580 Product Series features delivering innovative pump features for the water and wastewater industry, securing energy-efficient flow of water and wastewater in your pumping solutions. This robust and compact wall-mounted packaged drive has built-in pump application functionality such as sensorless flow calculation, multi-pump control, level control, soft pipe fill, dry run protection, quick ramps, and a solution for keeping the impeller of the pump clean. Usability is further enhanced with the intuitive Hand-Off-Auto control panel, the PC tool Drive composer, an optional Bluetooth® control panel, and a UL-approved electronic motor overload. The built-in energy calculator visualizes the energy savings achieved with the use of the drive.

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACQ580-PC-011A-6, 600 VAC, PLD 10HP, I2LD 11A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	22 lb
Product Net Depth / Length	12.63 in

Product Net Height	28.53 in
Product Net Width	6.42 in

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	50/60 Hz
Frame Size	R2
Input Voltage (U _{in})	525 ... 600 V

Additional Information

Product Name	-
--------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-PC - Drive with circuit breaker disconnect US