

PRODUCT-DETAILS

ACH480-04-06A9-2

LV AC drive module for HVAC, IEC: Pn 1.1 kW,
6.9 A, 200 V (ACH480-04-06A9-2)



General Information

Global Commercial Alias	ACH480-04-06A9-2
Product ID	3AXD50000646975
ABB Type Designation	ACH480-04-06A9-2
EAN	6438177640318
Catalog Description	LV AC drive module for HVAC, IEC: Pn 1.1 kW, 6.9 A, 200 V (ACH480-04-06A9-2)

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACH480-04-06A9-2 PN: 1.1 kW, IN: 6.9 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	4.455 dm ³
--------------	-----------------------

Dimensions		
Product Net Weight		1.7 kg
		3.748 lb
Product Net Depth / Length		208 mm
		8.189 in
Product Net Height		223 mm
		8.780 in
Product Net Width		73 mm
		2.874 in
Package Level 1 Depth / Length		282 mm
		11.102 in
Package Level 1 Height		273 mm
		10.748 in
Package Level 1 Width		148 mm
		5.827 in

Technical		
Number of Phases		3
Degree of Protection		IP20
Enclosure Type NEMA		Open Type
Sound dB (A)		63.10 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g	
Frame Size		R1
Communication Protocol		BACNET
		CAN
		DeviceNet
		EtherNet/IP
		LON
		MODBUS
		Other Bus Systems
		PROFIBUS
		PROFINET IO
		TCP/IP
Number of Hardware Interfaces	Industrial Ethernet	0
	Other	2
	Parallel	0
	PROFINET	0
	RS-232	0
	RS-422	0
	RS-485	1
	Serial TTY	0
	USB	1
Includes	Control unit	
	PC connection	
Analog Inputs		2
Analog Outputs		2
Number of Digital In/Outputs		6 / 3
Output Current, Heavy-Duty Use (I_{HD})		4.8 A
Output Current, Light-Overload Use (I_{LD})		6.6 A
Output Current, Normal Use (I_N)		6.9 A

Output Power, Heavy-Duty Use (P_{HD})	0.75 kW
Output Power, Light-Overload Use (P_{LD})	1.1 kW
Output Power, Normal Use (P_n)	1.1 kW
Apparent Power Output	4.8 kV·A
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current
0/25 %
0/50 %
0/100 %
50/25 %
50/50 %
50/100 %
90/50 %
90/100 %

Temperature Rating	Maximum 50 °C
--------------------	---------------

Additional Information	
Product Main Type	ACH480-04
Product Name	Base unit

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH480-04 - Drive module for HVAC	

