

PRODUCT-DETAILS

DSM06L-0KW2-302-S1NB0

DSM series motor, 220 VAC, flange size 60 mm, low inertia, 200 W, SmartAbs ST, no brake, key, seal



General Information

Global Commercial Alias	DSM06L-0KW2-302-S1NB0
Product ID	3AXD50000915378
ABB Type Designation	DSM06L-0KW2-302-S1NB0
Catalog Description	DSM series motor, 220 VAC, flange size 60 mm, low inertia, 200 W, SmartAbs ST, no brake, key, seal
Long Description	The DSM servo motor is a high performance servo motor. It is used together with the E530 servo drive. The DSM servo motor offers various options including: brake, oil seal, and encoder type, which provides flexible choices for customers. The 5 pole-pairs design makes it more compact in structure and effectively reduce the cogging torque.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	8501520000
Invoice Description	DSM series motor, 220 VAC, flange size 60 mm, low inertia, 200 W, SmartAbs ST, no brake, key, seal
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	1.1 kg
Product Net Depth / Length	119 mm
Product Net Height	72 mm
Product Net Width	60 mm
Package Level 1 Depth / Length	253 mm
Package Level 1 Height	105 mm
Package Level 1 Width	123 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP65
Input Voltage (U_{in})	220 V

Additional Information	
Product Name	DSM servo motor

Classifications	
UNSPSC	26101109

Categories	
Drives → Low Voltage AC Drives → Servo Products → AC servo motors → DSM servo motors	

