

## PRODUCT-DETAILS

# ACH480-04-048A-2

LV AC drive module for HVAC, IEC: Pn 11 kW,  
48 A, 200 V (ACH480-04-048A-2)



### General Information

Global Commercial Alias	ACH480-04-048A-2
Product ID	3AXD50000998920
ABB Type Designation	ACH480-04-048A-2
EAN	6438177702658
Catalog Description	LV AC drive module for HVAC, IEC: Pn 11 kW, 48 A, 200 V (ACH480-04-048A-2)

### Ordering

Country of Origin	China (CN) Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACH480-04-048A-2 PN: 11.0 kW, IN: 48 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

### Container Information

Gross Volume	13.393 dm³
--------------	------------

## Dimensions

Product Net Weight	5.6 kg 12.346 lb
Product Net Depth / Length	213 mm 8.386 in
Product Net Height	240 mm 9.449 in
Product Net Width	262 mm 10.315 in
Package Level 1 Depth / Length	356 mm 14.016 in
Package Level 1 Height	275 mm 10.827 in
Package Level 1 Width	290 mm 11.417 in

## Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Sound dB (A)	69 dB(A)
Multiple Battery Information	Lithium Coin, CR2032, 220 mAh, 3 V, 1 pc, 3 g
Frequency (f)	47 ... 63 Hz
Frame Size	R4
Communication Protocol	BACNET CAN DeviceNet EtherNet/IP LON MODBUS Other Bus Systems PROFIBUS PROFINET IO TCP/IP
Number of Hardware Interfaces	Industrial Ethernet 0 Other 2 Parallel 0 PROFINET 0 RS-232 0 RS-422 0 RS-485 1 Serial TTY 0 USB 1
Includes	Control unit PC connection
Analog Inputs	2
Analog Outputs	2
Number of Digital In/Outputs	6 / 3
Output Current, Heavy- Duty Use ( $I_{HD}$ )	32.0 A
Output Current, Light- Overload Use ( $I_{LD}$ )	46.2 A
Output Current, Normal Use ( $I_N$ )	48 A
Output Power, Heavy- Duty Use ( $P_{HD}$ )	7.5 kW
Output Power, Light- Overload Use ( $P_{LD}$ )	11.0 kW

Output Power, Normal Use ( $P_n$ )	11 kW
Apparent Power Output	33.3 kV·A
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current
0/25 %
0/50 %
0/100 %
50/25 %
50/50 %
50/100 %
90/50 %
90/100 %

Temperature Rating	Maximum 50 °C
--------------------	---------------

Additional Information

Product Main Type	ACH480-04
Product Name	Frequency converter

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for HVAC → ACH480-04 - Drive module for HVAC

