

PRODUCT-DETAILS

ACQ580-01-059A-2+B066

LV AC general purpose wall-mounted drive, UL:
Pld 59.4 Hp, 20 A, 460 V (ACQ580-01-059A-
2+B066)



General Information

Global Commercial Alias	ACQ580-01-059A-2+B066
Product ID	3AXD50001001988
ABB Type Designation	ACQ580-01-059A-2+B066
Catalog Description	LV AC general purpose wall-mounted drive, UL: Pld 59.4 Hp, 20 A, 460 V (ACQ580-01-059A-2+B066)

Long Description

Designed for harsh locations, the ACQ580-01 Type 4X / IP66 drive can withstand unfriendly environments with ease. The drive is resistant to various weather conditions from the snows of winter to the heat of summer. Indoors, it is resistant to water spray, dirt and chemicals and is NSF 169 certified for food splash zones. This drive is ideal for food and beverage, agriculture, livestock applications and for coastal areas. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACQ580 drives you can easily take full control of your processes to comprehensively manage your plant.

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure	piece
-------------------------	-------

Dimensions	
Product Net Weight	56 lb
Product Net Depth / Length	10.25 in
Product Net Height	25.47 in
Product Net Width	10.91 in

Technical	
Number of Phases	3
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	50/60 Hz
Input Voltage (U _{in})	208 ... 240 V

Additional Information	
Product Name	AC Drive

Categories	
Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ580-01 - Wall-mounted drive for water and wastewater	



