

## PRODUCT-DETAILS

# ACS580-01-014A-4+B066+F254

LV AC general purpose wall-mounted drive,  
UL: Pld 14 Hp, 10 A (ACS580-01-014A-  
4+B066+F254)



## General Information

Global Commercial Alias	ACS580-01-014A-4+B066+F254
Product ID	3AXD50001005290
ABB Type Designation	ACS580-01-014A-4+B066+F254
Catalog Description	LV AC general purpose wall-mounted drive, UL: Pld 14 Hp, 10 A (ACS580-01-014A-4+B066+F254)
Long Description	Designed for harsh locations, the ACS580-01 Type 4X / IP66 drive can withstand unfriendly environments with ease. The drive is resistant to various weather conditions from the snows of winter to the heat of summer. Indoors, it is resistant to water spray, dirt and chemicals and is NSF 169 certified for food splash zones. This drive is ideal for food and beverage, agriculture, livestock applications and for coastal areas. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant.

## Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure piece

Dimensions	
Product Net Weight	34 lb
Product Net Depth / Length	11.48 in
Product Net Height	23.86 in
Product Net Width	8.19 in

Technical	
Number of Phases	3
Degree of Protection	IP66
Enclosure Type NEMA	Type4X
Frequency (f)	60 Hz
Input Voltage (U <sub>in</sub> )	480 V

Additional Information	
Product Name	AC Drive

### Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-01 - Wall-mounted drive



