

PRODUCT-DETAILS

ACQ80-01-030KW-4

ACQ80-01-030KW-4 PN: 30 kW, IN: 62 A



General Information

Global Commercial Alias	ACQ80-01-030KW-4
Product ID	3AXD50001028985
ABB Type Designation	ACQ80-01-030KW-4
EAN	6438177707615
Catalog Description	ACQ80-01-030KW-4 PN: 30 kW, IN: 62 A

Ordering

Country of Origin	Finland (FI)
Customs Tariff Number	85044085
Invoice Description	ACQ80-01-030KW-4 PN: 30 kW, IN: 62 A
Made To Order	Yes
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	20 kg
Product Net Depth / Length	257 mm

Product Net Height	636 mm
Product Net Width	203 mm

Technical

Number of Phases	3
Degree of Protection	IP21
Sound dB (A)	69 dB(A)
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Mounting Type	Wall-mounted
Output Current, Heavy-Duty Use (I_{HD})	45 A
Output Current, Light-Overload Use (I_{LD})	58 A
Output Current, Normal Use (I_n)	62 A
Output Power, Heavy-Duty Use (P_{HD})	22.0 kW
Output Power, Light-Overload Use (P_{LD})	30 kW
Output Power, Normal Use (P_n)	30 kW
Temperature Rating	Maximum 40 °C Minimum -15 °C

Additional Information

Product Main Type	ACQ80-01
Product Name	Frequency converter

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industry-Specific Drives → Drives for water → ACQ80-01 - Wall-mounted drive for solar pump

