



PRODUCT-DETAILS

ACS580-01-07A3-4+B063+H376

No Description Available

General Information

Global Commercial Alias	ACS580-01-07A3-4+B063+H376
Product ID	3AXD50001050030
ABB Type Designation	ACS580-01-07A3-4+B063+H376
Catalog Description	No Description Available
Long Description	<p>Designed for harsh locations, the ACS580-01 Type 4X / IP66 drive can withstand unfriendly environments with ease. The drive is resistant to various weather conditions from the snows of winter to the heat of summer. Indoors, it is resistant to water spray, dirt and chemicals and is NSF 169 certified for food splash zones. This drive is ideal for food and beverage, agriculture, livestock applications and for coastal areas. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant.</p>

Additional Information

ABB Type Designation	ACS580-01-07A3-4+B063+H376
Country of Origin	United States (US)
Customs Tariff Number	85044080
Global Commercial Alias	ACS580-01-07A3-4+B063+H376
Gross Weight	0 kg
Made To Order	No
Medium Description	<p>Designed for harsh locations, the ACS580-01 Type 4X / IP66 drive can withstand unfriendly environments with ease. The drive is resistant to various weather conditions from the snows of winter to the heat of summer. Indoors, it is resistant to water spray, dirt and chemicals and is NSF 169 certified for food splash zones. This drive is ideal for food and beverage, agriculture, livestock applications and for coastal areas. Versatile and straightforward settings menu and assistants enable fast setup, commissioning, use and maintenance, while rugged and robust design makes it a good fit for various environments. With the ACS580 drives you can easily take full control of your processes to comprehensively manage your plant.</p>
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Product Name	AC Drive
Product Net Depth / Length	9.79 in
Product Net Height	20.55 in
Product Net Weight	28 lb
Product Net Width	8.19 in
Product Type	Undefined
Quote Only	No
Selling Unit of Measure	piece

Short Description

ACS580-01-07A3-4+B063+H376