

PRODUCT-DETAILS

# ACS280-04S-06A9-1

## ACS280-04S-06A9-1 PN: 0.75kW, IN: 6.9A



### General Information

Global Commercial Alias	ACS280-04S-06A9-1
Product ID	3AXD50001071509
ABB Type Designation	ACS280-04S-06A9-1
Catalog Description	ACS280-04S-06A9-1 PN: 0.75kW, IN: 6.9A

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS280-04S-06A9-1 PN: 0.75kW, IN: 6.9A
Made To Order	No
Minimum Order Quantity	10 piece
Order Multiple	10 piece
Quote Only	No
Selling Unit of Measure	piece

### Container Information

Gross Volume	30 cm³
--------------	--------

Dimensions	
Product Net Weight	0.95 kg
Product Net Depth / Length	90 mm
Product Net Height	145 mm
Product Net Width	135 mm
Package Level 1 Depth / Length	341 mm
Package Level 1 Height	225 mm
Package Level 1 Width	575 mm
Package Level 1 Units	10 carton

Technical	
Number of Phases	2
Degree of Protection	IP00
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage ( $U_{in}$ )	200 ... 240 V
Mounting Type	Module_NO UNIT\$
Output Current, Heavy-Duty Use ( $I_{HD}$ )	4.5 A
Output Current, Light-Overload Use ( $I_{LD}$ )	6.6 A
Output Current, Normal Use ( $I_n$ )	6.9 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	0.75 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	1.1 kW
Output Power, Normal Use ( $P_n$ )	1.1 kW

Additional Information	
Product Name	FREQUENCY CONVERTER

Classifications	
UNSPSC	39122001

---

## Categories

---

Drives → Low Voltage AC Drives → Machinery Drives → ACS280 - Machinery Cold-plate Drive

