


## PRODUCT-DETAILS

# 3BHE026284R0104

## UA D215 A104: PEC80 Converter Signal Int



### General Information

Product ID	3BHE026284R0104
ABB Type Designation	-
Catalog Description	UA D215 A104: PEC80 Converter Signal Int
Long Description	UA D215 A104: PEC80 Converter Signal Int

### Additional Information

ABB Type Designation	-
Country of Origin	Switzerland (CH)
Customs Tariff Number	85371092
Frame Size	Undefined
Gross Weight	0 kg
Invoice Description	UA D215 A104: PEC80 Converter Signal Int
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Gross Weight	0 kg
Package Level 1 Units	1 piece
Part Type	New
Product Name	-
Product Net Depth / Length	340 mm

Product Net Height	20 mm
Product Net Weight	0.22 kg
Product Net Width	110 mm
Product Type	Undefined
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Baden, Switzerland
WEEE Category	Product Not in WEEE Scope

Categories

Power Electronics → UNITROL® Excitation Systems → Static Excitation Systems → UNITROL 6000 X-power

