



PRODUCT-DETAILS

# EXC3BSE074053R1

## AIS880 Analog Input 4 to 20mA HI EXC

### General Information

Global Commercial Alias	EXC3BSE074053R1
Product ID	3BSE074053E1
ABB Type Designation	AIS880 Exchange
Catalog Description	AIS880 Analog Input 4 to 20mA HI EXC

### Additional Information

ABB Type Designation	AIS880 Exchange
Country of Origin	United States (US) Sweden (SE) Singapore (SG)
Customs Tariff Number	8538909999
Frame Size	Undefined
Global Commercial Alias	EXC3BSE074053R1
Gross Volume	80.159 cm <sup>3</sup>
Gross Weight	0.073 g
Invoice Description	AIS880 Analog Input 4 to 20mA HI EXC
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	105 mm
Package Level 1 Gross Weight	0.073 g
Package Level 1 Height	9.8 mm
Package Level 1 Units	1 piece
Package Level 1 Width	77.9 mm
Part Type	Exchange
Product Name	I-O Module
Product Net Depth / Length	105 mm
Product Net Height	9.8 mm
Product Net Weight	0.073 g
Product Net Width	77.9 mm
Product Type	I-O_Module
Quote Only	No

Selling Unit of Measure	piece
Stocked At (Warehouses)	Wickliffe, Ohio, United States Västerås, Sweden
Technical Information	AIS880 Analog Input Signal Conditioning Module High Integrity for 2/4-wire devices. 16 bit. HART communication. Certified for SIL3. Note! The replaced part with RMA to be returned according to T&C otherwise an extra charge will be required.
WEEE Category	Product Not in WEEE Scope