



PRODUCT-DETAILS

3BSE074057E1

DIS880 Digital Input 24V HI EXC

General Information

Product ID	3BSE074057E1
ABB Type Designation	DIS880 Exchange
Catalog Description	DIS880 Digital Input 24V HI EXC

Additional Information

ABB Type Designation	DIS880 Exchange
Country of Origin	United States (US) Sweden (SE) Singapore (SG)
Customs Tariff Number	8538909999
Frame Size	Undefined
Gross Volume	80.159 cm³
Gross Weight	0.073 kg
Invoice Description	DIS880 Digital Input 24V HI EXC
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	105 mm
Package Level 1 Gross Weight	0.073 kg
Package Level 1 Height	9.8 mm
Package Level 1 Units	1 piece
Package Level 1 Width	77.9 mm
Part Type	Exchange
Product Name	I-O Module
Product Net Depth / Length	105 mm
Product Net Height	9.8 mm
Product Net Weight	0.073 kg
Product Net Width	77.9 mm
Product Type	I-O_Module
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Wickliffe, Ohio, United States Västerås, Sweden

Technical Information	DIS880 Digital Input 24V Signal Conditioning Module High Integrity for 2/3/4-wire devices. Sequence of Events (SOE) enabled. Certified for SIL3. Note! The replaced part with RMA to be returned according to T&C otherwise an extra
-----------------------	--

charge will be required.

WEEE Category

Product Not in WEEE Scope
