

PRODUCT-DETAILS

3BSE074059R1

DOS880 Digital Output 24V 0.6A HI



General Information

Product ID	3BSE074059R1
ABB Type Designation	DOS880
Catalog Description	DOS880 Digital Output 24V 0.6A HI
Long Description	DOS880 a Digital Output 24 V / 0.6 A Signal Conditioning Module for High Integrity. Certified for SIL3.

Additional Information

Medium Description	Digital Output 24V 0.6A Signal Conditioning Module High Integrity. Certified for SIL3.
Product Type	I-O_Module
Technical Information	Exchange see 3BSE074059E1

Ordering

HS Code	853890-- Parts suitable for use solely or principally with the apparatus of heading 85.35, 85.36 or 85.37.- Other
Customs Tariff Number	85389099

Dimensions	
Product Net Depth / Length	105 mm
Product Net Height	9.8 mm
Product Net Width	77.9 mm
Product Net Weight	0.073 kg

Technical	
Channel Type	DI
Number of Output Channels	1

Environmental	
RoHS Status	Following EU Directive 2011/65/EU
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
Number of Batteries	0
SCIP	fc6c5439-91db-4a78-8c45-39eec4050e98 Sweden (SE)

Categories
Control System Products → I/O Products → Select I/O → Select I/O - Modules → DOS880 Digital Outputs → DOS880 Digital Output
Control Systems → 800xA → I/Os → Select I/O → I/O Modules

