

PRODUCT-DETAILS

# 3BSE078764R1

## AOS810 Analog Output 4 to 20mA



### General Information

Product ID	3BSE078764R1
ABB Type Designation	AOS810
Catalog Description	AOS810 Analog Output 4 to 20mA
Long Description	Analog Output Signal Conditioning Module for 2-wire devices. 16 bit. HART communication.

### Additional Information

Medium Description	Analog Output Signal Conditioning Module for 2-wire devices. 16 bit. HART communication.
Product Type	I-O_Module

### Ordering

HS Code	853890-- Parts suitable for use solely or principally with the apparatus of heading 85.35, 85.36 or 85.37.- Other
Customs Tariff Number	85389099

### Dimensions

Product Net Depth / Length	105 mm
Product Net Height	9.8 mm
Product Net Width	77.9 mm
Product Net Weight	0.073 kg

Technical

Channel Type	AO
Number of Output Channels	1

Environmental

RoHS Status	Following EU Directive 2011/65/EU
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
Number of Batteries	0
SCIP	b50b8fb4-8bda-4614-8260-d22cc63a9f24 Sweden (SE)

Categories

Control System Products → I/O Products → Select I/O → Select I/O - Modules → AOS810 Analog Outputs → AOS810 Analog Output 4 to 20mA

Control Systems → 800xA → I/Os → Select I/O → I/O Modules

