

PRODUCT-DETAILS

3BSE078768R1

DOS810 Digital Output 24V 0.6A



General Information

Product ID	3BSE078768R1
ABB Type Designation	DOS810
Catalog Description	DOS810 Digital Output 24V 0.6A
Long Description	Digital Output 24V 0.6A Signal Conditioning Module.

Additional Information

Medium Description	Digital Output 24V 0.6A Signal Conditioning Module.
Product Type	I-O_Module

Ordering

HS Code	853890-- Parts suitable for use solely or principally with the apparatus of heading 85.35, 85.36 or 85.37.- Other
Customs Tariff Number	85389099

Dimensions

Product Net Depth / Length	105 mm
----------------------------	--------

Product Net Height	9.8 mm
Product Net Width	77.9 mm
Product Net Weight	0.073 kg

Technical

Channel Type	DI
Number of Output Channels	1

Environmental

RoHS Status	Following EU Directive 2011/65/EU
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
Number of Batteries	0
SCIP	ce149c63-7621-4fd8-ba16-0bf56aafe04f Sweden (SE)

Categories

Control System Products → I/O Products → Select I/O → Select I/O - Modules → DOS810 Digital Outputs → DOS810 Digital Output 24V 0.6A

Control Systems → 800xA → I/Os → Select I/O → I/O Modules

