



PRODUCT-DETAILS

REP3BUR001454R1

DI814 Digital Input 24V Current 16 ch

General Information

Global Commercial Alias	REP3BUR001454R1
Product ID	3BUR001454F1
ABB Type Designation	DI814
Catalog Description	DI814 Digital Input 24V Current 16 ch

Additional Information

ABB Type Designation	DI814
Country of Origin	Sweden (SE)
Customs Tariff Number	8538909999
Frame Size	Undefined
Global Commercial Alias	REP3BUR001454R1
Gross Volume	0.001 m³
Gross Weight	0.2 kg
Invoice Description	DI814 Digital Input 24V Current 16 ch
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	102 mm
Package Level 1 Gross Weight	0.2 kg
Package Level 1 Height	119 mm
Package Level 1 Units	1 piece
Package Level 1 Width	45 mm
Part Type	Repair
Product Name	I-O Module
Product Net Depth / Length	102 mm
Product Net Height	119 mm
Product Net Weight	0.2 kg
Product Net Width	45 mm
Product Type	I-O_Module
Quote Only	No
Selling Unit of Measure	piece
Stocked At (Warehouses)	Malmö, Sweden
Technical Information	Repair of DI814 Digital Input 24V Current 16 ch