



PRODUCT-DETAILS

3GAA073310-BSHIN

(3GAA073310-BSHIN)

General Information	
Product ID	3GAA073310-BSHIN
ABB Type Designation	M2AAX 71MA6
Catalog Description	(3GAA073310-BSHIN)

Ordering	
ABB Type Designation	M2AAX 71MA6
Invoice Description	M2AAX 71MA6
Product Name	3-Phase squirrel cage motor
Product Type	IAA2__M2AAX_IE2
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	India (IN)
Customs Tariff Number	85015100

Electrical										
Electrical Data										
Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
Y	--	50 Hz	415 V	0.18 kW	900 r/min	0.64 A	0.620	56.60 %	1.90 N·m	3.50
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										50 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE2 Full Load (100%) 56.6 % Partial Load (75%) 54.6 % Partial Load (50%) 47.6 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides

Number of Poles (High)	6
Two Speed Motor	No
Type of Duty	S1
Voltage Code	S

Mechanical

Frame Material	Aluminum
Frame Size	71
Bearing	6203-2Z/C3
Bearing NDE	6202-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	5 kg
Gross Weight	8 kg

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → General Performance Motors → IE2 High Efficiency Aluminum Motors