

PRODUCT-DETAILS

3GAA081330-BPK

(3GAA081330-BPK)

"No longer for sale" replaced by 3GAA081330-



General Information

Product ID	3GAA081330-BPK
ABB Type Designation	M3AA 80MC 2
Catalog Description	(3GAA081330-BPK)

Ordering

ABB Type Designation	M3AA 80MC 2
Invoice Description	M3AA 80MC 2
Product Name	3-Phase squirrel cage motor
Product Type	3AA3_M3AA_IE3_AA
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Selling Unit of Measure	piece
Country of Origin	Finland (FI) Poland (PL)
Customs Tariff Number	85015220

Electrical

Electrical Data

Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor	Efficiency	Torque	IS/IN
D	--	50 Hz	200 V	1.10 kW	2883 r/min	4.60 A	0.810	83.90 %	3.60 N·m	7.90
D	--	60 Hz	230 V	1.10 kW	3500 r/min	4.10 A	0.780	84.00 %	3.00 N·m	9.90
Temperature Class Default										--
Altitude										1000 m
Ambient Temperature										40 °C
IC Class										IC411
IE Class Data (50 Hz)										IE Class IE3 Full Load (100%) 83.9 % Partial Load (75%) 83.6 % Partial Load (50%) 82.0 %
IE Class Data (60 Hz)										IE Class IE3 Full Load (100%) 84.0 % Partial Load (75%) 83.0 % Partial Load (50%) 80.2 %
IP Class										IP55
Insulation Class										ICLF
Direction of Rotation										Both sides
Number of Poles (High)										2
Two Speed Motor										No
Voltage Code										P

Mechanical

Frame Material	Aluminum
Frame Size	80
Bearing	6204-2Z/C3
Bearing NDE	6203-2Z/C3
IM Class	IMB5 IM3001
Terminator Box Location	D-End top

Dimensions

Package Level 1 Units	0 carton
Product Net Weight	10.5 kg
Gross Weight	13.5 kg

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
SCIP	27ac6190-e1ce-4080-8654-6552aaabbe58 Finland (FI)

Classifications

UNSPSC	26101100
--------	----------

Categories

Motors and Generators → IEC Low Voltage AC Motors → Process Performance Motors → IE3 Premium Efficiency Aluminum Motors

