



PRODUCT-DETAILS

3GAA082062-BSA

No Description Available

"No longer for sale" replaced by 3GAA082002-

General Information								
Product ID	3GAA082062-BSA							
ABB Type Designation	M1AA 80B 4							
Catalog Description	No Description Available							
Additional Information								
ABB Type Designation	M1AA 80B 4							
Altitude	1000 m							
Ambient Temperature	40 °C							
Bearing	6204-2Z/C3							
Bearing NDE	6204-2Z/C3							
Country of Origin	Türkiye (TR)							
Customs Tariff Number	85015220							
Direction of Rotation	Both sides							
Electrical Data								
	Conn	Temp Class	Freq	Voltage	Power	Speed	Current	Power Factor
	D	--	50 Hz	230 V	0.75 kW	1400 r/min	3.50 A	0.730
	Y	--	50 Hz	400 V	0.75 kW	1400 r/min	2.00 A	0.730
	Y	--	60 Hz	460 V	0.75 kW	1700 r/min	1.82 A	0.680
Frame Material	Aluminum							
Frame Size	80							
Gross Weight	0 kg							
IC Class	IC411							
IE Class Data (50 Hz)	IE Class IE1 Full Load (100%) 72.1 % Partial Load (75%) 71.6 % Partial Load (50%) 68.9 %							
IM Class	IMB5 IM3001							
Insulation Class	ICLF							
IP Class	IP55							
Made To Order	No							
Minimum Order Quantity	1 piece							
Number of Poles (High)	4							
Order Multiple	1 piece							
Package Level 1 Units	0 carton							
Product Name	3-Phase squirrel cage motor							
Product Net Weight	0 kg							
Product Type	1AA1__M1AA_IE1_AA							

Quote Only	No
Replacement Product ID (NEW)	3GAA082002-BSE
Selling Unit of Measure	piece
Standards	IEC 60034-1
Starting of Motor	Direct Online
Temperature Class Default	--
Terminator Box Location	D-End top
Two Speed Motor	No
Type of Duty	S1
UNSPSC	26101100
Voltage Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)